



Safety switch, with electromagnetic guard locking, coded, for safety locking device PSENSlock, guard locking for process protection, guard locking-independent safety outputs, holding force 1000 N, 8-pin M12 male connector, series connection Important information: This item is at the end of the product lifecycle and therefore will no longer be available in the foreseeable future. Please get in touch with your PILZ contact to find a suitable alternative or successor product.

Technical details

General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	gering
Classification to EN 60947-5-3:	PDDB
Transponder coding:	codiert
Suitable for series connection:	ja
unit type:	Sensor

Technical data

Electrical data

Supply voltage (V):	24
Type of supply voltage U1:	DC
Power consumption DC:	7.2

Inputs

Number of inputs:	3
DC voltage at input:	24 V DC

Semiconductor outputs

Number of OSSD outputs:	2
Number of sig. outputs:	1
S/C output short circuit proof:	ja

Utilisation cat. to EN 60947-1:	DC-12
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. F. bei 40 °C
EMC to standard ...:	EN 55011: class A, EN 60947-5-3, EN 62061
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Acc. shock to standard2:	10g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Protection type, housing:	IP67
Mechanical data	
Holding force magnet on:	1000
Max. vertical offset:	5 mm
Max. angular offset:	2,5 deg
Type 1 actuator:	PSEN sl-1.0 1.1
Type 2 actuator:	PSEN sl-1.0fm 1.1
Sensor can be flush-mounted:	Ja, Montagehinweis beachten
Connection type:	M12, 8-pin male
Cable lines:	LiYY 8 x 0,25 mm ²
Housing material upper part:	PBT
Material of base plate:	Anticorodal, hart eloxiert
Height dimension:	172
Width dimension:	45
Depth dimension:	44
Net weight:	1120

Gross weight:	1190
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365019
UNSPSC 25:	39122205
EAN-Code:	4046548078824
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
Volume:	0 dm3

Obligatory accessories



570620

PSEN sl-1.0 1.1 1actuator

Optional accessories












540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m

	540326	PSEN cable axial M12 8-pole 30m
	540320	PSEN cable axial M12 8-pole 5m
	540331	PSEN T junction (auxiliary contact) M12
	540342	PSEN cable M12-8sf M12-8sm, 10m
	540321	PSEN cable axial M12 8-pole 10m
	540343	PSEN cable M12-8sf M12-8sm, 20m
	540322	PSEN cable angle M12 8-pole 3m
	540333	PSEN cable M12-8sf, 20m
	540344	PSEN cable M12-8sf M12-8sm, 30m



540323

PSEN cable angle M12 8-pole 5m



540312

PSEN screw M5x20 10pcs



540328

PSEN Y junction M12-M12/M12



570550

PSEN sl bracket swing door



570551

PSEN sl bracket sliding door



540319

PSEN cable axial M12 8-pole 3m



540340

PSEN cable M12-8sf M12-8sm, 2m



540341

PSEN cable M12-8sf M12-8sm, 5m



773603

PDP67 F 4 code