

PSEN me5M NC-NO.NC-NO 1switch

6L000017



Mechanical safety gate system PSENmech, interlock principle magneticforce, contacts interlocking 1 N/C, 1 N/O, contacts guard locking 1 N/C, 1 N/O, supply voltage 24 V AC/DC.

Technical details

General data

Approval:	CSA, CE, CCC, UKCA, DGUV
Suitable for series connection:	yes
unit type:	Sensor

Technical data

Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	AC/DC

Relay outputs

Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	240 V
Max. current AC15 safety cont.:	1.5 A
Voltage DC13 safety cont.:	250 V

Environmental data

Ambient temperature:	-25 - 55 °C
Overvoltage category:	II

Mechanical data

Holding force:	1500 N
Height dimension:	192 mm
Width dimension:	42 mm

Depth dimension:	44 mm
Net weight:	489 g
Gross weight:	541 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
UNSPSC 25:	39122205
GTIN:	4046548101461
Volume:	1.258 dm ³
Harmonized System Code:	85365080
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories



6L000006

PSEN me5 20mm extension



6L000007

PSEN me5 40mm extension



6L000008

PSEN me5 emergency release front



6L000009

PSEN me5 emergency release back



6L000005

PSEN me5 escape release



570793

PSEN cable 200m-8x0.25mm²
