

MM A MINI-IO CAB01B 5.0m

772210



Motion Monitoring Adapter SI/HA 25/25, 5 m.

Technical details

General data

Approval: CE, UKCA, cULus Listed

Technical data

Environmental data

Ambient temperature: 0 - 60 °C

Condensation permitted?: Not permitted

Mechanical data

Connector type 1: 25-pin D-Sub male connector

Shape of connector type 1: straight

Connector type 2: 25-pin D-Sub female connector

Shape of connector type 2: straight

Connector type 3: 8-pin Mini-IO male connector

Shape of connector type 3: straight

Fixing screws: UNC 4-40

Housing material connector 3: PBT

Contact surfaces material 1: Au

Contact surfaces material 2: Au

Contact surfaces material 3: Au

Material of pins: Cu alloy

Material of sockets: Cu alloy

| | |
|---------------------------------|------------------------------|
| Length cable: | 5 m |
| Tolerance of cable length K1: | +/- 0.15 m |
| Colour cable insulation 1: | Green, similar to RAL6018 |
| Housing colour: | Black RAL 9005 |
| Material of cable insulation 1: | PUR |
| Trailing capability of cable 1: | yes |
| Bend radius (when laying) K1: | 8 x Ø |
| Max. outside diameter cable K1: | 6 - 6 mm |
| Conductor cross section: | 0.14 - 0.14 mm ² |
| Cable cross section AWG K1: | 26 |
| Shielding K1: | yes |
| Number of conductors: | 8 |
| Approvals for cable K1: | UL AWM-Style 20233 |
| Approvals for connector 1: | UL94 V-0 |
| Approvals for connector 2: | UL94 V-0 |
| Approvals for connector 3: | UL94 V-0 |
| Housing material: | TPE-SEBS UL 94 HB |
| Height dimension: | 38 mm |
| Width dimension: | 54.5 mm |
| Depth dimension: | 16 mm |
| Net weight: | 225 g |
| Gross weight: | 235 g |
| Environment | |
| WEEE klassifikation (08/2018): | 5 devices (feed size < 50cm) |
| Commercial data | |
| Harmonized System Code: | 85444290 |
| UNSPSC 25: | 26121603 |
| EAN-Code: | 4046548080513 |
| ECLASS version: | ECLASS-13 |

| | |
|---------------------------|----------|
| ECLASS Reference Feature: | 27060313 |
| ETIM Version: | ETIM-9.0 |
| ETIM Reference Group: | EG000026 |
| ETIM Reference Feature: | EC001855 |
| Volume: | 0 dm3 |