

PSEN op cable axial M12 4-p. shield. 5m

630304



Connection cable, PUR, yellow RAL1003, shielded, 4-pin, socket straight M12, on open line end, A-coded, cable length: 5m

Technical details

General data

Approval: CE, UKCA, cULus Listed

Technical data

Electrical data

Rated current:	4 A
Typ. conductor resistance K1:	57 Ohm/km
Specific contact resistance K1:	$\geq 7E+15$ Ohm*km
Specific conductor capacity K1:	65.6pF/m

Environmental data

Ambient temperature:	-25 - 80 °C
Pollution degree clear.&creep.:	3

Mechanical data

Connector type 1:	4-pin M12 female connector
Shape of connector type 1:	straight
Coding of M12 connector 1:	A coded
Contact surfaces material 1:	Au
Material of sockets:	CuSn
Cable material K1:	Cu
Insulation material cable K1:	PP (9Y)
Cable type K1:	Li9YC11Y

Length cable:	5 m
Material shield surface K1:	Sn
Colour cable insulation 1:	Yellow, similar to RAL 1003
Housing colour:	Black
Material of cable insulation 1:	TPU 11YH1, PUR
Trailing capability of cable 1:	no
Bend radius (when laying) K1:	5 x Ø
Max. outside diameter cable K1:	5.55 - 5.55 mm
Conductor cross section:	0.34 - 0.34 mm ²
Cable cross section AWG K1:	22
Shielding K1:	yes
Type of shielding K1:	Wire mesh
Number of conductors:	4
Approvals for cable K1:	UL AWM-Style 20233, UL/CSA
Approvals for connector 1:	UL94 V-0
Halogen-free:	yes
Oil resistance:	resistant
Flame resistance:	UL VW1
Housing material:	PUR
Net weight:	254 g
Gross weight:	264 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1

CAS No.:	7439-92-1
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548002195
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060311
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855
Volume:	0.867 dm ³