

## PSEN op cable angle M12 4-p. shield. 3m

630306



Connection cable, PUR, yellow RAL1003, shielded, 4-pin, socket angled M12, on open line end, A-coded, cable length: 3m

## Technical details

### General data

Approval: CE, UKCA, cULus Listed

### Technical data

#### Electrical data

Rated current:	4 A
Typ. conductor resistance K1:	57 Ohm/km
Specific contact resistance K1:	$\geq 7E+15$ Ohm*km
Specific conductor capacity K1:	65.6pF/m

#### Environmental data

Ambient temperature:	-25 - 80 °C
Pollution degree clear.&creep.:	3

#### Mechanical data

Connector type 1:	4-pin M12 female connector
Shape of connector type 1:	angled
Coding of M12 connector 1:	A coded
Contact surfaces material 1:	Au
Material of sockets:	CuSn
Cable material K1:	Cu
Insulation material cable K1:	PP (9Y)
Cable type K1:	Li9YC11Y

Length cable:	3 m
Material shield surface K1:	Sn
Colour cable insulation 1:	Yellow, similar to RAL 1003
Housing colour:	Black
Material of cable insulation 1:	TPU 11YH1, PUR
Trailing capability of cable 1:	no
Bend radius (when laying) K1:	5 x Ø
Max. outside diameter cable K1:	5.55 - 5.55 mm
Conductor cross section:	0.34 - 0.34 mm <sup>2</sup>
Cable cross section AWG K1:	22
Shielding K1:	yes
Type of shielding K1:	Wire mesh
Number of conductors:	4
Approvals for cable K1:	UL AWM-Style 20233, UL/CSA
Approvals for connector 1:	UL94 V-0
Halogen-free:	yes
Oil resistance:	resistant
Flame resistance:	UL VW1
Housing material:	PUR
Net weight:	163 g
Gross weight:	170 g
<b>Environment</b>	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
<b>Commercial data</b>	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548002171
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060311

ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855
Volume:	0 dm <sup>3</sup>