

PSEN me5M NC.NC n 1 switch

6L000021



Mechanical safety gate system PSENmech, with M12 connection 5-pin, interlock principle magnetic force, contacts interlocking 1 N/C, contacts guard locking 1 N/C, supply voltage 24 V AC/DC.

Technical details

General data

| | |
|---------------------------------|--------------------------|
| Approval: | CSA, CE, CCC, UKCA, DGUV |
| Suitable for series connection: | yes |
| unit type: | Sensor |

Technical data

Electrical data

| | |
|----------------------------|-----------|
| Supply voltage (V): | 24 - 24 V |
| Type of supply voltage U1: | AC/DC |

Relay outputs

| | |
|---------------------------------|--------------|
| Utilisation cat. AC15/DC13sta.: | EN 60947-5-1 |
| Voltage DC13 safety cont.: | 24 V |

Environmental data

| | |
|-----------------------|-------------|
| Ambient temperature: | -25 - 55 °C |
| Overvoltage category: | II |

Mechanical data

| | |
|-------------------|-----------------|
| Holding force: | 1500 N |
| Connection type: | M12, 5-pin male |
| Height dimension: | 192 mm |
| Width dimension: | 42 mm |
| Depth dimension: | 44 mm |

| | |
|--------------------------------|--------------------------------|
| Net weight: | 489 g |
| Gross weight: | 541 g |
| Environment | |
| RoHS directive: | 2011/65/EU, 2015/863/EU |
| RoHS conformity: | yes |
| RoHS exceptions: | yes |
| RoHS except.s acc. to direct.: | 6c |
| REACH compliance: | contains min. 1 SVHC-substance |
| REACH included substances: | Lead |
| %-part of the pollutant: | > 0,1 |
| CAS No.: | 7439-92-1 |
| SCIP entry available: | yes |
| WEEE classification (08/2018): | 5 devices (feed size < 50cm) |
| Commercial data | |
| ECLASS version: | ECLASS-13 |
| ECLASS Reference Feature: | 27272603 |
| ETIM Version: | ETIM-9.0 |
| ETIM Reference Group: | EG000026 |
| ETIM Reference Feature: | EC002593 |
| UNSPSC 25: | 39122205 |
| GTIN: | 4046548101508 |
| Volume: | 1.258 dm3 |
| Harmonized System Code: | 85365019 |
| Type of tariff number: | TARIC |
| Use of customs tariff number: | Ausfuhr, Einfuhr |
| Quantity per packaging unit: | 1 |

Optional accessories



380209

PSS67 Cable M12sf M12sm, 5m



630347

PSEN op cable angle M12 5-pole 3m



540308

PSEN screw M4x10 10pcs




630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



540309

PSEN screw M4x12 10pcs



630350

PSEN op cable angle M12 5-pole 30m







630298

PSEN cable M12-5sf 20m



380320

PSS67 I/O Cable

| | | |
|---|----------|------------------------------------|
|  | 630310 | PSEN op cable axial M12 5-pole 3m |
|  | 630297 | PSEN op cable axial M12 5-pole 30m |
|  | 380220 | PSS67 cable M12-5sf, M12-5sm, 20m |
|  | 380208 | PSS67 Cable M12sf M12sm, 3m |
|  | 6L000006 | PSEN me5 20mm extension |
|  | 6L000007 | PSEN me5 40mm extension |
|  | 6L000008 | PSEN me5 emergency release front |
|  | 6L000009 | PSEN me5 emergency release back |
|  | 540310 | PSEN screw M4x16 10pcs |



540311

PSEN screw M5x10 10pcs



6L000005

PSEN me5 escape release



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630364

PSEN op cable axial M12 5-pole 50m



380210

PSS67 Cable M12sf M12sm, 10m



630365

PSEN op cable angle M12 5-pole 50m



380211

PSS67 Cable M12sf M12sm, 30m



380214

PSS67 Cable M12af M12am, 10m



380710

PDP67 Cable M12-5sf M12-5sm, 0.5m



380215

PSS67 Cable M12af M12am, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380713

PDP67 Cable M12-5sf M12-5sm, 2m



380711

PDP67 Cable M12-5sf M12-5sm, 1m



380712

PDP67 Cable M12-5sf M12-5sm, 1.5m
