

PMCcable M4/C2B6/010/2Q5/S1

8177352

Hybrid cable assembled on both sides: connectors <> con.23 round connector 9-pin speedtec; No. of wires and cross section (4x2,5+(2x1,0)+(2xAWG22)); suitable for PMCprotego D.01-24 and the motors PM Ctendo SZ.4x...K bis SZ.73...K with HDSL encoder; Length 10m;

Technical details

| | |
|---------------------------------|--------------------------------|
| Technical data | |
| Environmental data | |
| Ambient temperature: | -20 - 80 °C |
| Mechanical data | |
| Connector type 1: | 9-pin M23 female connector DSL |
| Shape of connector type 1: | straight |
| Connector type 2: | 6-pin plug-in connector PC5 |
| Connector type 3: | 15-pin D-Sub male connector |
| Shape of connector type 3: | straight |
| Housing material connector 3: | GD-Zn |
| Contact surfaces material 1: | Au |
| Contact surfaces material 2: | Sn |
| Contact surfaces material 3: | Au |
| Length cable: | 10 m |
| Material shield surface K1: | Sn |
| Colour cable insulation 1: | Orange |
| Material of cable insulation 1: | TPU |
| Trailing capability of cable 1: | yes |
| Bend radius (when laying) K1: | 5 x Ø |
| Max. outside diameter cable K1: | 14.2 - 15 mm |

| | |
|--------------------------------|--------------------------------|
| Cross section data cable K1: | (4 x 2.5+(2 x 1.00)+(2xAWG22)) |
| Shielding K1: | yes |
| Type of shielding K1: | Wire mesh |
| Net weight: | 3610 g |
| Gross weight: | 4150 g |
| Environment | |
| WEEE klassifikation (08/2018): | 5 devices (feed size < 50cm) |
| Commercial data | |
| UNSPSC 25: | 26121603 |
| EAN-Code: | 4046548092110 |
| ECLASS version: | ECLASS-13 |
| ETIM Version: | ETIM-9.0 |
| ETIM Reference Group: | EG000026 |
| ETIM Reference Feature: | EC001855 |