

## PNOZ XV1P C 3/24VDC 2n/o 1n/o t

787601



Safety relay (standalone), inputs: 1/2-channel wiring with/without detection of shorts across contacts, outputs: 2 N/O, 1 N/Ot-d (t = 0.1 - 3 s), automatic/monitored start, UB = 24 V DC, width: 22.5 mm, plug-in spring-loaded terminals, monitoring of E-STOP, safety gates, light curtain.

## Technical details

### General data

Approval: CCC, CE, UKCA, cULus Listed, TÜV, EAC (Eurasian)

### Technical data

### Electrical data

Supply voltage (V): 24 - 24 V

Type of supply voltage U1: DC

Power consumption DC: 3.5 W

### Inputs

Number of inputs: 2

### Semiconductor outputs

Number of semicond. outputs: 0

### Relay outputs

Utilisation cat. AC/DC1 stand.: EN 60947-4-1

Voltage AC1 safety cont.: 240 V

Max. current AC1 safety cont.: 5 A

Voltage DC1 safety cont.: 24 V

Max. current DC1 safety cont.: 5 A

Utilisation cat. AC15/DC13sta.: EN 60947-5-1

Voltage AC15 safety cont.: 230 V

Max. current AC15 safety cont.: 1.5 A

Voltage DC13 safety cont.:	24 V
Safety contacts: AC at UL:	240 VAC G. P.
Safety contacts: pilot duty:	C300, R300
Relay contact material:	AgSnO2
Addit. contact details relay:	+ 0.2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-10 - 55 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61000-6-3, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III / II
Pollution degree clear.&creep.:	2
Times	
Tolerance Tv:	-20 %/+20 %
Repetition accuracy:	2 %
Mechanical data	
Mounting position:	any
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Spring-loaded terminal
Terminal style:	plug-in
Height dimension:	101 mm
Width dimension:	22.5 mm
Depth dimension:	121 mm
Net weight:	230 g
Gross weight:	235 g
Environment	

RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead oxide
%-part of the pollutant:	> 0,1
CAS No.:	1317-36-8
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
<b>Commercial data</b>	
Harmonized System Code:	85364900
UNSPSC 25:	39122331
EAN-Code:	4046548008036
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449
Volume:	0.300 dm <sup>3</sup>

## Optional accessories

374290

PNOZ X Set spring loaded terminals P1+P2

