

PMCcable M4/B1B6/020/1Q5/S1

8177314

Hybrid cable assembled on both sides: Crimp connectors <> con.23 round connector 9-pin speedtec; No. of wires and cross section (4x1,5+(2x0,75)+(2xAWG22)); suitable for PM Ctendo DD5 and the motors PM Ctendo SZ.3x...K bis SZ.73...K with HDSL encoder; Length 20m;

Technical details

Technical data	
Environmental data	
Ambient temperature:	-20 - 80 °C
Mechanical data	
Connector type 1:	9-pin M23 female connector DSL
Shape of connector type 1:	straight
Connector type 2:	Crimp connector
Connector type 3:	15-pin D-Sub male connector
Shape of connector type 3:	straight
Housing material connector 3:	GD-Zn
Contact surfaces material 1:	Au
Contact surfaces material 2:	Sn
Contact surfaces material 3:	Au
Length cable:	20 m
Material shield surface K1:	Sn
Colour cable insulation 1:	Orange
Material of cable insulation 1:	TPU
Trailing capability of cable 1:	yes
Bend radius (when laying) K1:	5 x Ø
Max. outside diameter cable K1:	12.7 - 13.5 mm

Cross section data cable K1:	(4 x 1.5+(2 x 0.75)+(2xAWG22))
Shielding K1:	yes
Type of shielding K1:	Wire mesh
Net weight:	5390 g
Gross weight:	6190 g
Environment	
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
UNSPSC 25:	26121603
EAN-Code:	4046548091694
ECLASS version:	ECLASS-13
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855