

PMCtendo DD4.20/162/230-480V

4105573



Servo amplifier; Technical data at 3 x 400 V AC: Continuous output current: 20 A; I_{max} (5 s) = 40 A; Power consumption in S1 mode: 14 kVA Integral brake resistor incl. relay AS (restart interlock).

Technical details

General data	
Approval:	CE, UKCA, cULus Listed
Technical data	
Electrical data	
Purpose of U1:	Mains supply
Supply voltage (V):	230 - 480 V
Type of supply voltage U1:	AC
Purpose of U2:	supply
Supply voltage 2 (V):	24 - 24 V
Type of supply voltage U2:	DC
Power section	
Peak current for 5 s:	40 A
Analog inputs	
Number of analogue inputs:	2
Type of analogue inputs:	Voltage
Resolution of analogue inputs:	14 Bit, 12 Bit
Inputs	
U input to EN 61131-2 Type 1:	24 V DC
Analogue outputs	
Number of analogue outputs:	2

Type of analogue outputs:	Voltage
Resolution, analogue outputs:	10 Bit
CANopen interface	
Number of CANopen interfaces:	1
Serial interface	
Number of RS 232 interfaces:	1
Mechanical data	
Height dimension:	325 mm
Width dimension:	120 mm
Depth dimension:	265 mm
Net weight:	7500 g
Gross weight:	8800 g
Environment	
RoHS conformity:	yes
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85044085
UNSPSC 25:	39121007
EAN-Code:	4046548032697
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023101
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC001857
Volume:	0