

PMC SC6A062Y/EC 2x 4,5A

8C000065



Technical data at 3 x 400 V AC: Nominal output current: 2x 4.5 A @ 4kHz / 2x 4.0 A @ 8kHz. I_{max}: 210% for 2s / 250% for 2s. Apparent power: 2x 3.1 KVA. Without brake resistor. Option: Safety module SY6 (STO and SS1 using FSoE) and EtherCat.

Technical details

General data

Approval: UL Listed, CE, UKCA

Technical data

Electrical data

Supply voltage with phases: 3x400 VAC, +32/-50 %, 50/60 Hz, 3x480 VAC, +10/-58 %, 50/60 Hz

Supply voltage 2 (V): 24 - 24 V

Type of supply voltage U2: DC

Inputs

Environmental data

Ambient temperature: 0 - 45 °C

Cooling type: Built-in fan

Mechanical data

Height dimension: 343 mm

Width dimension: 45 mm

Depth dimension: 265 mm

Net weight: 3650 g

Gross weight: 5250 g

Environment

WEEE classification (08/2018): 5 devices (feed size < 50cm)

Commercial data

Harmonized System Code:	85044085
UNSPSC 25:	39121007
EAN-Code:	4046548100853
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023101
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC001857
Volume:	0

Obligatory accessories



8C000062

PMC SC6A062 terminal set (Y/Z)