

PNOZ m2p base module press function

773120



Configurable safe small controllers PNOZmulti Classic, base unit, expandable, with press functionality, ser. Interface RS232, 20 safe digital inputs, 4 safe semiconductor outputs, 2 safe relay outputs.

Technical details

General data

Approval: CE, UKCA, cULus Listed, KCC, KOSHA, EAC (Eurasian), TÜV

Technical data

Electrical data

Purpose of U1: System supply

Supply voltage (V): 24 - 24 V

Type of supply voltage U1: DC

Purpose of U2: Supply of SC outputs

Supply voltage 2 (V): 24 - 24 V

Type of supply voltage U2: DC

Potential isolation U2: Yes

Inputs

Max. no. live inputs: $U_B \leq 26.4 \text{ V} : 20$, $U_B > 26.4 \text{ V} : 15$

Signal level at input at 0: -3 - +5 VDC

U input to EN 61131-2 Type 1: 24 V DC

Potential isolation input: No

Semiconductor outputs

Number of semicond. outputs: 4

Potential isolation of S/C O: Yes


S/C output short circuit proof: Yes

Semiconductor outputs (standard)	
Number of auxiliary outputs:	1
Galv. isol. n/safe SC O:	Yes
Short circ. prot. n/safe S/C O:	Yes
Signal level at 1 n/safe S/C O:	UB - 0.5 VDC at 0.5 A
Test clock outputs	
Number of test pulse outputs:	4
Relay outputs	
Number of relay outputs:	2
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240 V
Max. current AC1 safety cont.:	6 A
Voltage DC1 safety cont.:	24 V
Max. current DC1 safety cont.:	6 A
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230 V
Max. current AC15 safety cont.:	3 A
Voltage DC13 safety cont.:	24 V
Pot. isolation relay outputs:	Yes
Cascading output as standard output	
Number of cascading outputs:	1
Galv. isol. casc. aux. S/C O:	No
Serial interface	
Number of RS 232 interfaces:	1
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	0 - 0 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-30, EN 60068-2-78

Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	15g
Clearance & creepage dist. to:	EN 61131-2
Overvoltage category:	III
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Potential separation	
Potential isolation 1 between:	SC output and system voltage
Type of potential isolation 1:	Safe separation
Potential isolation 2 between:	RL output and system voltage
Type of potential isolation 2:	Safe separation
Mechanical data	
Mounting position:	horizontal on top hat rail
DIN-rail dimensions:	35 x 7.5 EN 50022
Housing material lower section:	PPO UL 94 V0
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal, Spring-loaded terminal
Flex. cond. c/s AWG info:	24 - 16 AWG
Cond.flex AWG w/o crimp conn.:	24 - 12 AWG
Height dimension:	94 mm
Width dimension:	135 mm
Depth dimension:	121 mm
Net weight:	499 g
Gross weight:	519 g
Environment	

REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85371091
UNSPSC 25:	39122331
EAN-Code:	4046548013146
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242207
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC000236
Volume:	1.68

Obligatory accessories



773010B

Basic Licence for PNOZmulti Config.



779211

Chipcard 1 piece 32kB



793100

PNOZ m1p/m0p plug in screw terminals



779201

PNOZmulti Chipcard 1 piece 8kb




305160

PSS Conv USB / RS 232

783100

PNOZ m1p Set spring loaded terminals



Optional accessories

773010R

Time lim Licence 3Mth for PNOZmulti Conf

773010S

Time lim Licence 2Mth for PNOZmulti Conf

773010Q

Time lim Licence 4Mth for PNOZmulti Conf


779200

PNOZmulti Chipcard Set 10 piece 8KB



773010L

Lite Licence for PNOZmulti Config.



779212

PNOZmulti Chipcard Set 10 pieces 32kB



779250

PNOZmulti Seal 12 pieces





779240

PNOZmulti Chipcard Holder (Sparepart)



779230

PNOZ Chip Card Reader



779000

PNOZmulti Tool Kit



779110

PNOZmulti Bus-Terminator



773010V


User Upgr Licence for PNOZmulti Config

773011W

Project Upgr Licence for PNOZmulti Serv

773010W

Project Upgr Licence f. PNOZmulti Config



773011U

Basic Upgr Licence for PNOZmulti Service



773010U

Basic Upgr Licence for PNOZmulti Config




773011V

User Upgr Licence for PNOZmulti Service




774639

KOP-XE




773011B

Basic Licence for PNOZmulti Service




773011K

User Licence for PNOZmulti Service



773010K

User Licence for PNOZmulti Config



773011L

Lite Licence for PNOZmulti Service

773011G

Project Licence for PNOZmulti Service

773010G

Project Licence for PNOZmulti Config